



tesapack[®] ultra strong

Product Information

BNR 57176, 51124, 57177, 57174, 57175, 58644, 58645

Product Description

tesapack[®] ultra strong is a heavy-duty packaging tape. It is equipped for demanding applications calling for the extra security of a highly tear-proof tape.

Product Features

- Highly tear-proof PVC backing
- Natural rubber adhesive ensures excellent adhesion
- High sealing security
- For packaging and bundling of heavy goods
- Even, low-noise unwinding
- Suitable for use with all available tesapack[®] hand dispensers

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------|-------------------|-------|
| • Backing material | PVC film | • Total thickness | 65 µm |
| • Type of adhesive | natural rubber | | |

Properties/Performance Values

- | | | | |
|--------------------------|--------------------|-----------------------|-----------|
| • Tensile strength | 60 N/cm | • Low noise unwinding | yes |
| • Adhesive strength | Very high adhesion | • Solvent free | no |
| • Ageing resistance (UV) | no | • Suitable surfaces | Cardboard |
| • Hand tearability | no | • Tear resistance | yes |

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?cp=NaN>