
Your Expert Partner for **Human Machine Interfaces**

Indicator element

Distribution by
Rs-online

84-8001.9340



https://rs-online.eao.com/component/84-8001.9...

Your product:



84-8001.9340
Indicator element

OPERATING-/INDICATION PART

Illumination colour: White

ELECTRICAL CHARACTERISTICS

Operating voltage: 12 V DC ±10 %

MECHANICAL CHARACTERISTICS

Terminal: Flat ribbon cable

Weight: 0.009 kg

AMBIENT CONDITION

IP Protection: IP40

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER


Short Description: Indicator element, White, Single-LED, 12 V DC ±10 %, Flat ribbon cable

Kind of illlumination: Single-LED

Hints: LED and built-in resistor included
Standard version: Cable length 300 mm
Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67)
Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occure, the plugs may become loose

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED

Wiring diagrams:



Component layouts:

