






Normal Geometric Tolerancing				
	-	//	≡	⊥
0 to 100	0.2			0 to 10 0.2
over 100 to 150	0.3	0.3		over 10 0.3
over 150	0.5			

Normal Dimension Tolerances			
0<U<=30	±0.25	30<U<=53	±0.30
53<U<=70	±0.35	70<U<=90	±0.44
90<U<=115	±0.55		



印字面 (印刷白色)

NOTES:

- Input Data :
 Rated input voltage : DC 5~30V
 Max. Switching frequency : 10k Hz
- Output Data :
 Rated Switching voltage : DC 5~30V
 Rated Switching current : 100 mA
- General Data :
 Impulse withstand voltage : 2.5kV
 Screw Torque Value: 0.4N.m
 Suitable Electric Wire: 24~12 (2.5mm²)

REV.	CONTENT	CHK.	DATE

DWG.	W.ZJ	DATE	14.05.21	UNITS	MM	SHEET/OF	1 / 1
CHK.		DATE		SCALE	1.5:1 (:)		
APP.		DATE		NAME	RE-0014		
				DWG NO.	SP-03-RE001400		

ITEM	NAME OF PART	MATERIAL	NOTES
1	RE-0014-W		