

EYSEO 360° surveillance indoor camera

Item no. SVIP20000



-
- High-resolution 3K/5-megapixel indoor camera with pan/tilt function for 360° room monitoring
 - Ready to use straight away thanks to super-simple set-up via the EYSEO app
 - In the handy Privacy Mode, the lens tilts downwards – keeping your private life comfortably private
 - Free access to the live stream and all app features – no subscription required
 - Many smart features such as person tracking, line crossing detection, privacy zone masking, IR and white light LEDs, and two-way audio
 - An intuitive app makes it easy to manage video data in everyday life
 - Compact, discreet and elegant design – to suit any home décor
 - Simple and flexible installation – whether on a table or on the ceiling
 - Voice control via Alexa and Google available
-

360° home security camera – keep an eye on everything, at all times

The compact EYSEO indoor camera with pan and tilt functionality is a high-performance 360° camera for your home. Thanks to its all-round view and high-resolution image quality, you won't miss a single important moment – no matter where you are.

Privacy mode for maximum security

In privacy mode, the camera lens automatically tilts downwards and stops recording. This ensures that private matters remain private.

Keep an eye on children and pets at all times

EYSEO 360° surveillance indoor camera

Item no. SVIP20000

With this security camera, you'll always know what's happening at home. The built-in motion detection sends push notifications with a preview image straight to your smartphone. Two-way communication lets you listen and speak – conveniently via the app. The camera is versatile and can be placed on a stand or mounted on the ceiling.

Smart detection and automatic tracking

The smart indoor camera reliably recognises people and pets, detects directional line crossings and automatically tracks people within its field of view.

Voice control with Alexa & Google Assistant

Control your 360° camera with voice commands, receive voice notifications or view live footage on an Echo Show.

Clear images day and night

Infrared LEDs ensure sharp black-and-white images at night. When motion is detected, white light LEDs enable colour night-time footage.

Recording without a subscription

Videos are stored locally on a microSD card with up to 1 TB capacity. The free EYSEO app for iOS and Android offers shared access, Do Not Disturb mode and push notifications with thumbnails.

EYSEO 360° surveillance indoor camera

Item no. SVIP20000

Dimensions	(WxH) 74 x 114.5 mm
Number of users	5
Number of presets	3
Number of streams	2
Number of simultaneous connections	5
Item weight	0.5 kg
Product range	Comfort
Audio	Built-in: microphone, speaker
Audio bitrate	8000, 16000 kbps
Audio compression	G.711A, G.711U
Audio output	1 x built-in speaker
Audio input	1 x built-in microphone
Resolution	3K (2880 x 1620 pixels)
Resolution modes	Main stream: 2880 x 1620; Substream: 1280 x 720, 640 x 480, 640 x 360
Recording modes	Motion, VCA, Duration, Noise
Interface type	USB-C
Motion detection	Intrusion, Line Crossing, Enter Region, Leave Region
Image sensor	1/2.7" CMOS
Image settings	Automatic mode / Colour mode

Pixels (effective)	2880 (H) x 1620 (V) px
Frame rate	20
Aperture	F2.0
Width	74 mm
Focal length	2.8 mm
Digital zoom	Yes
Electronic shutter	1/5 to 1/20,000 s
Backlight compensation	DWDR, HLC, BLC
Housing material	Plastic
Horizontal field of view	110°
Height	114.5 mm
Camera type	Dome
Speaker	1 x built-in, 1 W
Power consumption	7.2 W
Material	Plastic
Max. resolution @ frame rate	2880 x 1620 @ 20 frames per second
Max. operating temperature	45 °C
Max. relative humidity	90 %
Min. operating temperature	-10 °C
Minimum illumination (colour)	0.001 lx
Mobile access	Yes

EYSEO 360° surveillance indoor camera

Item no. SVIP20000

Network protocols	P2P, DHCP, RTSP, SMTP, DDNS, HTTP, HTTPS, Google Drive
Network connection: Wi-Fi	Wi-Fi 6, 2.4 GHz / 5 GHz
ONVIF	Yes
Lens mount	M12
PTZ control	Manual, person tracking, preset
Privacy zones	4 (linked to preset 1)
Noise reduction	3D DNR
Pan/tilt range	Horizontal 350° / Vertical 110°
Power supply DC	5 V
Storage medium	Optional microSD card (max. 1 TB)
Current consumption	600 mA
Power supply	USB-C, 5 V DC / 1.5 A
Day/night switching	ICR/Colour/B&W, VCA-controlled between IR and white light
Depth	74 mm
Supported browsers	Google Chrome, Microsoft Edge
Shutter speed	1/5 to 1/20,000 s
Encryption	HTTPS, TLS 1.2/1.3
Vertical field of view	58.1°
Video bitrate	128 kbit/s to 2 Mbit/s, CBR/VBR

Video Content Analysis (VCA)	Person, vehicle, pet
Video compression	H.265 / H.264
WEEE group	09
Web server	Yes
White balance	Automatic / manual
White light range (up to)	10 m
Horizontal beam angle	110°
EAN	4043813005783