


C9T, Film, Metallized Polypropylene, AC Filter, 108 uF, -5/+15%, 415 VAC



General Information

Supplier:	KEMET
Series:	C9T
Dielectric:	Metallized Polypropylene
Style:	Can
Features:	Three Phase PFC
RoHS:	Yes
Lead:	Quick Connect
Qualifications:	VDE
Miscellaneous:	Q = 17.5 kvar. Operating Freq. = 50 Hz

Dimensions

D	75mm +/-0.5mm
L	280mm +/-2mm

Packaging Specifications

Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag
Packaging Quantity:	12

Specifications

Capacitance:	108 uF
Capacitance Tolerance:	-5/+15%
Voltage AC:	415 VAC
Temperature Range:	-25/+55C
Rated Temperature:	55°C
Max dV/dt:	30 V/us
Ripple Current:	32 Amps

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.