



# BLACKWELDER

## WELDING GLOVES



PPE Category II







	EN388:2016
Resistance to abrasion: Blade cut resistance: Tear resistance: Puncture resistance: Blade cut resistance according to ISO13997 :	<b>Levels :</b> ●●●○ ●●●● ●●●○ ●●●○ D
	EN407
Burning behaviour: Contact heat: Convective heat: Radiant heat: Small splashes of molten metal: Large splashes of molten metal:	<b>Levels :</b> ●●●● ●○○○ ●●●○ ●○○○ ●●●● X
Sizes	Packaging
7 – 8 – 9 - 10 – 11 – 12	10 per packet / 60 per box

Welding glove with palm in waterproof brown split leather, back in waterproof black grain leather. Lined with 100% para-aramid thread and mineral filament. Elastic tightening on the back. 15 cm cuff in waterproof black split leather. 100% para-aramid sewing thread.

### THE + PRODUCT

- 
**SOFTNESS**
- 
**RESISTANCE**
- 
**COMFORT**

### RELEVANT SECTORS

- 
Automotive manufacturing and supply industry
- 
Assembly works
- 
Metal manufacturing and processing industry
- 
Welding works
- 
Engineering industry and industrial maintenance
- 
Building and public works