

278500**Manual bending tool set**

Code	ETIM
1589830	EC011119
EAN	UNSPSC
4017981278508	27-11-25-01
Country of origin	eCl@ss
Germany	21-04-16-03
Customs tariff number	
82055980	

**Article description**

- Sizes from 3 to 10 mm Ø to 180°
- For precision steel pipes EN 10305-3 (DIN 2394), hydraulic pipes EN 10305-1 (DIN 2391) with 0.75 - 1.0 mm wall thicknesses as well as bendable stainless steel pipes with 1.0 mm wall thicknesses
- With 5 aluminium bending formers for pipes with Ø 3-4, 5, 6, 8 and 10 mm
- For clamping in a vice or useable as bending pliers

Article parts list

1 basic tool body 3-10 mm No. 278570,1 bending lever 3-10 mm No. 278581,5 aluminium bending formers for pipes with Ø 3-4, 5, 6, 8, 10 mm

Article information

Contents [Qty of pieces] 1 Net weight [kg] 1,2 kg