

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (4% in Contact/Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Hand solderable with tin/lead solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2273000-1
M8 x 1.0 straight plug Pigtail



TE Part #2-1879074-3
THS15 50R 5%



TE Part #CONSMA007
SMA Plug 50 Ohm Cable Crimp



TE Part #ADP-SMAM-SMAM-G
SMA Plug to SMA Plug



TE Part #CONSMA007-G
SMA Plug 50 Ohm Cable Crimp




TE Part #T4073014031-001
M8.FMLE.PNLFRONT.3POS.STR WIRE



TE Part #CONSMA007-R178
SMA Plug 50 Ohm Cable Crimp



TE Part #CONSMA007-R58
SMA Plug 50 Ohm Cable Crimp



TE Part #EM6977-000
X4-0.6-0-SP



TE Part #T4033014031-000
M8.FMLE.PNLFRONT.3POS.STR

Documents

Product Drawings

SMP STRAIGHT CABLE JACK DIRECT SOLDER

English

CAD Files

Customer View Model

ENG_CVM_1056521-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_1056521-1_D.3d_stp.zip

English

Customer View Model

ENG_CVM_1056521-1_D.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets



Instruction Sheet (U.S.)

English