

# SFP Transceivers & Direct Attach Cables



## SFP / SFP+ / QSFP+ Transceivers

### Cisco Compatible

Part Number	Data Transfer Rate	Type	Connection	Distance
GLCLHSMDST	1 Gbps	Single & Multi Mode Fiber	LC	10 km (6.2 mi)
GLCSXMMMDST	1 Gbps	Multi Mode fiber	LC	550 m (1804 ft)
SFP10GSRST	10 Gbps	Multi Mode fiber	LC	300 m (984 ft)
SFP10GLRST	10 Gbps	Single Mode Fiber	LC	10 km (6.2 mi)
QSFP40GLR4ST	40 Gbps	Single Mode fiber	LC	10km (6.2mi)

### HP / HPE Compatible

J4859CST	1 Gbps	Single & Multi Mode Fiber	LC	10 km (6.2 mi)
J4858CST	1 Gbps	Multi Mode Fiber	LC	550 m (1804 ft)
JD092BST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
J9151AST	10 Gbps	Single Mode Fiber	LC	10 km (6.2 mi)
J9150AST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
JL563A-ST	10 Gbps	Copper	RJ-45	30 m (98.4 ft)
813874B21ST	10 Gbps	Copper	RJ-45	30 m (98.4 ft)

### Juniper Compatible

EXSFP1GESXST	1 Gbps	Multi Mode Fiber	LC	550 m (1804 ft)
EXSFP1GETST	1 Gbps	Copper	RJ-45	100 m (328 ft)
RXGETSFPST	1 Gbps	Copper	RJ-45	100 m (328 ft)
SFP1GETST	1 Gbps	Copper	RJ-45	100 m (328 ft)
EXSFP10GESRS	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
EXSFP10GELRS	10 Gbps	Single Mode Fiber	LC	10 km (6.2 mi)

## Benefits of our SFP Transceivers & Direct Attach Cables (DAC)

- **100% compatibility guarantee** – Built and tested to OEM specifications and reliability tested to eliminate deployment headaches.
- **True lifetime warranty** – No catches or hassles; easy product replacement – we stand behind our SFPs.
- **No risk** – Buy from a leader in IT hardware and support, trusted by IT professionals around the world.
- **Easy to find and buy globally** – Wide distribution and sales network allows easy standardization on StarTech.com SFPs across multiple geographic locations.

View our selection of SFP Transceivers & Direct Attach Cables at:  
[www.startech.com/SFPs](http://www.startech.com/SFPs)

# SFP Transceivers & Direct Attach Cables



## SFP / SFP+ / QSFP+ Transceivers

### Cisco Meraki Compatible

Part Number	Data Transfer Rate	Type	Connection	Distance
MASFP10GBSR	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
MASFP10GBLR	10 Gbps	Single Mode Fiber	LC	10 km (6.2 mi)
MASFP1GBSXST	1000 Mbps (1 Gbps)	Multi Mode Fiber	LC	550 m (1804 ft)
MASFP1GBTXST	10/100/1000 Mbps	Copper	RJ-45	100 m (328 ft)

### Arista Networks Compatible

AR-SFP-1G-T-ST	1 Gbps	Copper	RJ-45	100 m (328 ft)
AR-SFP-10G-SR-ST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
AR-SFP-10G-T-ST	10 Gbps	Copper	RJ-45	30 m (98.4 ft)

### Extreme Networks Compatible

10302-ST	10 Gbps	Single Mode Fiber	LC	10 km (6.2 mi)
10301-ST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
10301-T-ST	10 Gbps	Copper	RJ-45	30 m (98.4 ft)

### Brocade Compatible

44W4408-ST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
XBR-000180-ST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)

### Palo Alto Networks Compatible

PLUS-LR-ST	10 Gbps	Single Mode Fiber	LC	10 km (6.2 mi)
PLUS-SR-ST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)
PLUS-T-ST	10 Gbps	Copper	RJ-45	30 m (98.4 ft)

### Citrix Compatible

EG3D0000086-ST	1 Gbps	Multi Mode Fiber	LC	550 m (1804 ft)
EW3F0000710-ST	10 Gbps	Multi Mode Fiber	LC	300 m (984 ft)

### Dell Compatible

SFP1GLXEMCST	1 Gbps	Single Mode Fiber	LC	10 km (6.2 mi)
--------------	--------	-------------------	----	----------------

# SFP Transceivers & Direct Attach Cables



## SFP / SFP+ / QSFP+ Direct Attach Cables

### Cisco Compatible

Part Number	Data Transfer Rate	Type	Connection	Distance
SFPCMM2M	Copper SFP+ Cable	10 Gbps	Passive DAC	2m
QSFPH40GACU7	Copper QSFP+ Cable	40 Gbps	Active DAC	7 m (23 ft)
SFPH10GBCU6M	Copper SFP+ Cable	10 Gbps	Passive DAC	6 m (20 ft)
SFPH10GACU10	Copper SFP+ Cable	10 Gbps	Active DAC	10 m (33 ft)

### HP / HPE Compatible

J9283BST	Copper SFP+ Cable	10 Gbps	Passive DAC	3 m (9.8 ft)
J9281BST	Copper SFP+ Cable	10 Gbps	Passive DAC	1 m (3.3 ft)
JG326AST	Copper QSFP+ Cable	40 Gbps	Passive DAC	1 m (3.3 ft)

### Juniper Compatible

EXSFP10GE1M	Copper SFP+ Cable	10 Gbps	Passive DAC	1 m (3.3 ft)
QFXQSFPDAC1M	Copper QSFP+ Cable	40 Gbps	Passive DAC	1 m (3.3 ft)
EXSFP10GEDA5	Copper SFP+ Cable	10 Gbps	Passive DAC	5 m (16.4 ft)

### Dell Compatible

DACSFP10G1M	Copper SFP+ Cable	10 Gbps	Passive DAC	1 m (3.3 ft)
-------------	-------------------	---------	-------------	--------------

## Why StarTech.com?



**Free pre & post sales support**  
from trained tech advisors.  
(Mon. - Fri.)



**Product reliability & performance**  
ensured by warranties, certifications  
and rigorous testing.



**Immediate availability:**  
Get the products you need when and  
where you need them.