

02 01 225

High Leverage Combination Pliers



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- High-grade special tool steel, forged, multi stage oil-hardened

Article No.	02 01 225
EAN	4003773010548
Pliers	black atramentized
Head	polished
Handles	plastic coated
Cutting capacities hard wire (diameter) Ø mm	3,0
Cutting capacities piano wire (diameter) Ø mm	2,5
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	14,0
Cutting capacity copper cable, multiple-stranded mm ²	25
Length mm	225
Net weight g	358



technical change and errors excepted

