

DATASHEET



NCLED36EM

**230V IP65 4FT 36W LED Non-Corrosive Fitting
1180mm EM3**

www.mlaccessories.co.uk

| MLA PART CODE | NCLED36EM |
|----------------------------|--|
| DESCRIPTION | 230V IP65 4FT 36W LED Non-Corrosive Fitting 1180mm EM3 |
| NET WEIGHT (KG) | 1.55 |
| FINISH | Grey |
| DIFFUSER | Opal |
| DIMENSIONS (MM) | Length - 1180 Width - 86 Projection - 66 |
| CONSTRUCTION | Construction - Polycarbonate |
| CLASS | II |
| IP RATING | IP65 |
| WATTAGE (W) | 36 |
| LAMP TECHNOLOGY | SMD LED |
| LAMP INCLUDED | Yes |
| LUMENS (LM) | 3000±5% |
| EFFICACY (LM/W) | 82.29 |
| LUMENS EMERGENCY MODE (LM) | 390±5% |
| CIRCUIT WATTAGE (W) | 35.83 |
| CCT | 4000K |
| LIGHT COLOUR | Cool White |
| CRI | >85 |
| LIFE SPAN (HRS) | 30,000 |
| DIMMABLE | No |
| EMERGENCY | Maintained / Non-maintained / Switched |
| INPUT VOLTAGE | 230V 50Hz |
| CABLE ENTRY (MM) | 20 |
| CABLE GLAND INCLUDED | Compression gland |
| BATTERY INCLUDED | Yes |
| WARRANTY | 3year(s) |
| WARRANTY INFORMATION | (excluding battery) |

| | |
|--|---------------|
| ORIGIN OF MANUFACTURE | China |
| DECLARATION OF CONFORMITY (HELD ON FILE) | Yes |
| EAN | 5055832937340 |

Date Created: 10/01/2022 22:57

