ROHM

MCR01MZPJ*** Thick Film Chip Resistors KIT

Ordner No : RSKT-MCR01 RS Stock No:5198528

- Technology: Thick film
- Package Inch / Size: 0402 / 1005
- Series: E24 + Jumper
- Resistor Range: 10Ω to1MΩ + Jumper
- Tolerance: ±5 %
- Maximum Wattage: 0.063 W
- Maximum Voltage: 50 V
- Resistor Values: 122
- Resistor Pieces per value: 200
- Operating Temperature: –55 to +155
- Temperature Coefficient: ±200 ppm

Binder Dim. : 250×300×35 mm
Weight. : 1300 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	MCR01MZPJ000	0 Ω
2	MCR01MZPJ100	10 Ω
3	MCR01MZPJ110	11 Ω
4	MCR01MZPJ120	12 Ω
5	MCR01MZPJ130	13 Ω
6	MCR01MZPJ150	15 Ω
7	MCR01MZPJ160	16 Ω
8	MCR01MZPJ180	18 Ω
9	MCR01MZPJ200	20 Ω
10	MCR01MZPJ220	22 Ω
11	MCR01MZPJ240	24 Ω
12	MCR01MZPJ270	27 Ω
13	MCR01MZPJ300	30 Ω
14	MCR01MZPJ330	33 Ω
15	MCR01MZPJ360	36 Ω
16	MCR01MZPJ390	39 Ω
17	MCR01MZPJ430	43 Ω
18	MCR01MZPJ470	47 Ω
19	MCR01MZPJ510	51 Ω
20	MCR01MZPJ560	56 Ω
21	MCR01MZPJ620	62 Ω
22	MCR01MZPJ680	68 Ω
23	MCR01MZPJ750	75 Ω
24	MCR01MZPJ820	82 Ω
25	MCR01MZPJ910	91 Ω
26	MCR01MZPJ101	100 Ω
27	MCR01MZPJ111	110 Ω
28	MCR01MZPJ121	120 Ω
29	MCR01MZPJ131	130 Ω
30	MCR01MZPJ151	150 Ω
31	MCR01MZPJ161	160 Ω
32	MCR01MZPJ181	180 Ω
33	MCR01MZPJ201	200 Ω
34	MCR01MZPJ221	220 Ω
35	MCR01MZPJ241	240 Ω
36	MCR01MZPJ271	270 Ω
37	MCR01MZPJ301	300 Ω
38	MCR01MZPJ331	330 Ω
39	MCR01MZPJ361	360 Ω
40	MCR01MZPJ391	390 Ω
41	MCR01MZPJ431	430 Ω
42	MCR01MZPJ471	470 Ω
43	MCR01MZPJ511	510 Ω
44	MCR01MZPJ561	560 Ω
45	MCR01MZPJ621	620 Ω
46	MCR01MZPJ681	680 Ω
47	MCR01MZPJ751	750 Ω
48	MCR01MZPJ821	820 Ω
49	MCR01MZPJ911	910 Ω
50	MCR01MZPJ102	1 kΩ

No	Manufacturer part number	Resistance
51	MCR01MZPJ112	1.1 kΩ
52	MCR01MZPJ122	1.2 kΩ
53	MCR01MZPJ132	1.3 kΩ
54	MCR01MZPJ152	1.5 kΩ
55	MCR01MZPJ162	1.6 kΩ
56	MCR01MZPJ182	1.8 kΩ
57	MCR01MZPJ202	2 kΩ
58	MCR01MZPJ222	2.2 kΩ
59	MCR01MZPJ242	2.4 kΩ
60	MCR01MZPJ272	2.7 kΩ
61	MCR01MZPJ302	3 kΩ
62	MCR01MZPJ332	3.3 kΩ
63	MCR01MZPJ362	3.6 kΩ
64	MCR01MZPJ392	3.9 kΩ
65	MCR01MZPJ432	4.3 kΩ
66	MCR01MZPJ472	4.7 kΩ
67	MCR01MZPJ512	5.1 kΩ
68	MCR01MZPJ562	5.6 kΩ
69	MCR01MZPJ622	6.2 kΩ
70	MCR01MZPJ682	6.8 kΩ
71	MCR01MZPJ752	7.5 kΩ
72	MCR01MZPJ822	8.2 kΩ
73	MCR01MZPJ912	9.1 kΩ
74	MCR01MZPJ103	10 kΩ
75	MCR01MZPJ113	11 kΩ
76	MCR01MZPJ123	12 kΩ
77	MCR01MZPJ133	13 kΩ
78	MCR01MZPJ153	15 kΩ
79	MCR01MZPJ163	16 kΩ
80	MCR01MZPJ183	18 kΩ
81	MCR01MZPJ203	20 kΩ
82	MCR01MZPJ223	22 kΩ
83	MCR01MZPJ243	24 kΩ
84	MCR01MZPJ273	27 kΩ
85	MCR01MZPJ303	30 kΩ
86	MCR01MZPJ333	33 kΩ
87	MCR01MZPJ363	36 kΩ
88	MCR01MZPJ393	39 kΩ
89	MCR01MZPJ433	43 kΩ
90	MCR01MZPJ473	47 kΩ
91	MCR01MZPJ513	51 kΩ
92	MCR01MZPJ563	56 kΩ
93	MCR01MZPJ623	62 kΩ
94	MCR01MZPJ683	68 kΩ
95	MCR01MZPJ753	75 kΩ
96	MCR01MZPJ823	82 kΩ
97	MCR01MZPJ913	91 kΩ
98	MCR01MZPJ104	100 kΩ
99	MCR01MZPJ114	110 kΩ
100	MCR01MZPJ124	120 kΩ

No	Manufacturer part number	Resistance
101	MCR03EZPJ134	130 kΩ
102	MCR03EZPJ154	150 kΩ
103	MCR03EZPJ164	160 kΩ
104	MCR03EZPJ184	180 kΩ
105	MCR03EZPJ204	200 kΩ
106	MCR03EZPJ224	220 kΩ
107	MCR03EZPJ244	240 kΩ
108	MCR03EZPJ274	270 kΩ
109	MCR03EZPJ304	300 kΩ
110	MCR03EZPJ334	330 kΩ
111	MCR03EZPJ364	360 kΩ
112	MCR03EZPJ394	390 kΩ
113	MCR03EZPJ434	430 kΩ
114	MCR03EZPJ474	470 kΩ
115	MCR03EZPJ514	510 kΩ
116	MCR03EZPJ564	560 kΩ
117	MCR03EZPJ624	620 kΩ
118	MCR03EZPJ684	680 kΩ
119	MCR03EZPJ754	750 kΩ
120	MCR03EZPJ824	820 kΩ
121	MCR03EZPJ914	910 kΩ
122	MCR03EZPJ105	1 MΩ

ROHM

MCR03EZPJ*** Thick Film Chip Resistors KIT

Ordner No : RSKT-MCR03 RS Stock No:5021917

- Technology: Thick film
- Package Inch / Size: 0603 / 1608
- Series: E24 + Jumper
- Resistor Range: 10Ω to1MΩ + Jumper
- Tolerance: ±5 %
- Maximum Wattage: 0.1 W
- Maximum Voltage: 50 V
- Resistor Values: 122
- Resistor Pieces per value: 100
- Operating Temperature: –55 to +155
- Temperature Coefficient: ±200 ppm

Binder Dim. : 250×300×35 mm
Weight. : 1300 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	MCR03EZPJ000	0 Ω
2	MCR03EZPJ100	10 Ω
3	MCR03EZPJ110	11 Ω
4	MCR03EZPJ120	12 Ω
5	MCR03EZPJ130	13 Ω
6	MCR03EZPJ150	15 Ω
7	MCR03EZPJ160	16 Ω
8	MCR03EZPJ180	18 Ω
9	MCR03EZPJ200	20 Ω
10	MCR03EZPJ220	22 Ω
11	MCR03EZPJ240	24 Ω
12	MCR03EZPJ270	27 Ω
13	MCR03EZPJ300	30 Ω
14	MCR03EZPJ330	33 Ω
15	MCR03EZPJ360	36 Ω
16	MCR03EZPJ390	39 Ω
17	MCR03EZPJ430	43 Ω
18	MCR03EZPJ470	47 Ω
19	MCR03EZPJ510	51 Ω
20	MCR03EZPJ560	56 Ω
21	MCR03EZPJ620	62 Ω
22	MCR03EZPJ680	68 Ω
23	MCR03EZPJ750	75 Ω
24	MCR03EZPJ820	82 Ω
25	MCR03EZPJ910	91 Ω
26	MCR03EZPJ101	100 Ω
27	MCR03EZPJ111	110 Ω
28	MCR03EZPJ121	120 Ω
29	MCR03EZPJ131	130 Ω
30	MCR03EZPJ151	150 Ω
31	MCR03EZPJ161	160 Ω
32	MCR03EZPJ181	180 Ω
33	MCR03EZPJ201	200 Ω
34	MCR03EZPJ221	220 Ω
35	MCR03EZPJ241	240 Ω
36	MCR03EZPJ271	270 Ω
37	MCR03EZPJ301	300 Ω
38	MCR03EZPJ331	330 Ω
39	MCR03EZPJ361	360 Ω
40	MCR03EZPJ391	390 Ω
41	MCR03EZPJ431	430 Ω
42	MCR03EZPJ471	470 Ω
43	MCR03EZPJ511	510 Ω
44	MCR03EZPJ561	560 Ω
45	MCR03EZPJ621	620 Ω
46	MCR03EZPJ681	680 Ω
47	MCR03EZPJ751	750 Ω
48	MCR03EZPJ821	820 Ω
49	MCR03EZPJ911	910 Ω
50	MCR03EZPJ102	1 kΩ

No	Manufacturer part number	Resistance
51	MCR03EZPJ112	1.1 kΩ
52	MCR03EZPJ122	1.2 kΩ
53	MCR03EZPJ132	1.3 kΩ
54	MCR03EZPJ152	1.5 kΩ
55	MCR03EZPJ162	1.6 kΩ
56	MCR03EZPJ182	1.8 kΩ
57	MCR03EZPJ202	2 kΩ
58	MCR03EZPJ222	2.2 kΩ
59	MCR03EZPJ242	2.4 kΩ
60	MCR03EZPJ272	2.7 kΩ
61	MCR03EZPJ302	3 kΩ
62	MCR03EZPJ332	3.3 kΩ
63	MCR03EZPJ362	3.6 kΩ
64	MCR03EZPJ392	3.9 kΩ
65	MCR03EZPJ432	4.3 kΩ
66	MCR03EZPJ472	4.7 kΩ
67	MCR03EZPJ512	5.1 kΩ
68	MCR03EZPJ562	5.6 kΩ
69	MCR03EZPJ622	6.2 kΩ
70	MCR03EZPJ682	6.8 kΩ
71	MCR03EZPJ752	7.5 kΩ
72	MCR03EZPJ822	8.2 kΩ
73	MCR03EZPJ912	9.1 kΩ
74	MCR03EZPJ103	10 kΩ
75	MCR03EZPJ113	11 kΩ
76	MCR03EZPJ123	12 kΩ
77	MCR03EZPJ133	13 kΩ
78	MCR03EZPJ153	15 kΩ
79	MCR03EZPJ163	16 kΩ
80	MCR03EZPJ183	18 kΩ
81	MCR03EZPJ203	20 kΩ
82	MCR03EZPJ223	22 kΩ
83	MCR03EZPJ243	24 kΩ
84	MCR03EZPJ273	27 kΩ
85	MCR03EZPJ303	30 kΩ
86	MCR03EZPJ333	33 kΩ
87	MCR03EZPJ363	36 kΩ
88	MCR03EZPJ393	39 kΩ
89	MCR03EZPJ433	43 kΩ
90	MCR03EZPJ473	47 kΩ
91	MCR03EZPJ513	51 kΩ
92	MCR03EZPJ563	56 kΩ
93	MCR03EZPJ623	62 kΩ
94	MCR03EZPJ683	68 kΩ
95	MCR03EZPJ753	75 kΩ
96	MCR03EZPJ823	82 kΩ
97	MCR03EZPJ913	91 kΩ
98	MCR03EZPJ104	100 kΩ
99	MCR03EZPJ114	110 kΩ
100	MCR03EZPJ124	120 kΩ

No	Manufacturer part number	Resistance
101	MCR03EZPJ134	130 kΩ
102	MCR03EZPJ154	150 kΩ
103	MCR03EZPJ164	160 kΩ
104	MCR03EZPJ184	180 kΩ
105	MCR03EZPJ204	200 kΩ
106	MCR03EZPJ224	220 kΩ
107	MCR03EZPJ244	240 kΩ
108	MCR03EZPJ274	270 kΩ
109	MCR03EZPJ304	300 kΩ
110	MCR03EZPJ334	330 kΩ
111	MCR03EZPJ364	360 kΩ
112	MCR03EZPJ394	390 kΩ
113	MCR03EZPJ434	430 kΩ
114	MCR03EZPJ474	470 kΩ
115	MCR03EZPJ514	510 kΩ
116	MCR03EZPJ564	560 kΩ
117	MCR03EZPJ624	620 kΩ
118	MCR03EZPJ684	680 kΩ
119	MCR03EZPJ754	750 kΩ
120	MCR03EZPJ824	820 kΩ
121	MCR03EZPJ914	910 kΩ
122	MCR03EZPJ105	1 MΩ