

Features

- BSP 1/2in thread
- Ball locking union
- Zinc plated Steel
- Nitrile rubber O-ring
- Double shut off
- Compatible with:
Faster ANV Series
Hansen HA 15000
Intertraco A Series
Safeway S565

RS PRO 1/2in BSP Quick Connect Union Coupling

RS Stock No.: 745-4693



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A female union hydraulic quick-connect coupling suitable for a G 1/2in connection enabling the quick connection and release in hydraulic or fluid transfer systems. The coupling is designed to shut off fluid flow instantly to prevent leakage.

General Specifications

Series	RS PRO
Compatible With	Faster ANV Series, Hansen HA 15000 (Gromelle), Intertraco A Series, Safeway S565, Stucchi BIR Series
Type	Union
Gender	Female
Locking Style	Ball Lock
Thread Size	1/2in
Thread Standard	BSP
Thread Gender	Male; Female
Material	Steel
Finish	Zinc Plated
Seal Material	Nitrile Rubber
Maximum Operating Pressure	250bar
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	125°C

Mechanical Specifications

Length	66mm
Diameter	38mm
Wrench Flats	27mm

Approvals

Compliance/Certifications	ISO 7241-A, ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007
---------------------------	-----------------------------------------------------------

Similar Products

Size (in)	Gender	Diameter (mm)	Length (mm)	Stock No
1/4	Female	25	48	745-4704
3/8	Female	31	57	745-4716
1/2	Female	38	66	745-4693
3/4	Female	48	82.5	745-4697
1	Female	56	100	745-4729
1/4	Male	22	38.6	745-4700
3/8	Male	26.5	39	745-4722
1/2	Male	31	44	745-4710
3/4	Male	40	55	745-4707
1	Male	47	66	745-4713