

PXP6060/2M00 Datasheet

Product Name // Plastic Body Overmoulded HDMI Cable
PXP6060 Range HDMI Plug to Sealed HDMI Plug 2M Cable

 [View Product Page](#)



// Product Description:

- Pre-Wired Plastic Body Overmoulded HDMI Cable
- Water and dustproof to IP68 & IP69K when mated with compatible connector
- 30 degree push twist locking, tamperproof lock prevents accidental un-mating
- Choice of cable lengths
- PXP6081 Sealing Cap available separately to maintain IP rating of unmated connectors
- Mate with 6000 Series HDMI Panel Mount Connectors

// General Information:

Product Display Title:	HDMI Plug to Sealed HDMI Plug 2M Cable
Product Family:	Circular Data Connectors
Product Series:	6000 Series - HDMI Buccaneer
Body Material:	Polycarbonate/Polybutylene Terephthalate (PC/PBT)
Body Material Type:	Plastic Body
Cable Length:	2m
Contact Type:	Plug Contact
Coupling Type:	Push-Twist
Data Cable Type:	HDMI Plug to Sealed HDMI Plug 2M Cable
Diameter Over Coupling Ring Mm:	32mm
Flamability Rating:	UL94V-0
Function:	Flex to Standard Connector Double Ended Cable
Ip Rating:	IP66, IP68, IP69K
Max Operating Temperature:	+70°C
Min Operating Temperature:	0°C
Number Of Contacts:	19 Contacts
Voltage Max:	5V

// Product PDF Links



// Product 3D CAD Model Links



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)