

2005 0511

Tool trolley

Code
1803018

ETIM
EC011808


EAN
4010886851654

UNSPSC
56-12-18-02

Country of origin
Germany

eCI@ss
21-07-11-00

Customs tariff number
94032080



Article description

- Body:
 - Dimensions: H 812 x W 771 x D 478 mm
 - Working platform in ABS, with compartments for small parts
 - Manoeuvrable and easy to steer with drive/steer handle
 - Side walls with Euro perforation 10 x 38 mm for attaching hooks and tools
 - Heel and impact protection for your safety
 - Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Drawers:
 - Central locking with cylinder lock
 - Wide drawers (W 640 x D 400 mm) fully extendable, removable
 - Safety locking per drawer, one-hand operation
 - Guide rails with ball bearings
 - Can be individually equipped with lengthwise and crosswise dividers (can be ordered individually)
 - Load capacity per drawer 40 kg, bottom heavy-duty drawer 60 kg
 - Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
 - GEDORE High-performance chassis:
 - Total load capacity 1000 kg static (750 kg dynamic)
 - 2 GEDORE heavy-duty wheels with roller bearings (fixed castors, 200 mm)
 - 2 GEDORE easy-running wheels with ball bearings (swivel castors, 125 mm), both with total brake each
 - The GEDORE trapezoidal axle construction secures smooth running, manoeuvrability and track-keeping also in case of maximum loads
- Accessories:
 - Length- (LT) and crosswise (QT) dividers from zinc-plated sheet steel (can be ordered individually)
 - Can be equipped with GEDORE tool modules (1500 ES/1500 CT or 2005 CT)
 - Optionally extendable with GEDORE tool chests, rear panels and tool holders
 - Further drawer versions upon request
 - Special colours and designs on request
 - Delivery without tools and accessories

Article information

Contents [Qty of pieces]	1	Number of drawers	7
Net weight [kg]	83 kg	Load capacity per drawer [kg]	40 kg
Total length [mm]	865 mm	Drawer type	5x Type 1, H = 67 mm 1x Type 2, H = 137 mm 1x Type 3, H = 207 mm
Total width [mm]	605 mm	Fixed roller diameter [2x]	200
Total height [mm]	1.020 mm	Swivel castor diameter with brakes [2x]	125
Surface	powder-coated	Single pull-out stop	no
Material	sheet steel	Number of wheels	4
Colour	GEDORE blue, RAL 5017	Working height	985
Dimension (L x W x H)	1.020 mm x 605 mm x	Static load carrying capacity [kg]	1000 kg
Load capacity kg	750 kg	Load capacity heavy duty drawer [kg]	60 kg
Number of crosswise dividers	2	RAL colour tone	blue
Number of lengthwise dividers	3		