

Handling module HSW-10-AS

Part number: 540226

FESTO



 General operating condition

Data sheet

Feature	Value
Working stroke	9 mm ... 15 mm
Size	10
Max. linear stroke with 90° swivel angle	90/90 mm
Z stroke	80 mm ... 100 mm
Cushioning	Noise reduction via buffers
Mounting position	optional
Design	Force pilot operated motion sequence
Position detection	Via proximity switch
Repetition accuracy end positions	+/-0.02 mm
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. drive torque at drive shaft	0.85 Nm
Max. axial force at drive shaft	10 N
Max. moment Mx	0.6 Nm
Max. moment My	0.6 Nm
Max. moment Mz	0.6 Nm
Max. effective load	0.5 kg
Max. radial force at drive shaft	30 N
Max. process force in Y direction	30 N
Product weight	1200 g
Type of mounting	Via through-hole and centring sleeve
Material stops	High-alloy steel
Material spring pressure piece	High-alloy steel
Material base plate	Wrought aluminium alloy Anodised
Material retaining bracket	Anodised
Material cross-guide	Tempered steel
Material swivel lever	Case-hardened steel Burnished
Material slotted guide plate	Case-hardened steel Hardened
Material sensor rail	Wrought aluminium alloy Anodised
Material bar	Wrought aluminium alloy Anodised
Material setting screw	High-alloy steel