

## DSS611Z

|                      |             |
|----------------------|-------------|
| Battery Type         | Lithium-ion |
| Charging Time        | 22 min      |
| Body only machine    | 1           |
| Voltage              | 18 v        |
| Depth of Cut @ 90°   | 57 mm       |
| Blade Diameter       | 165 mm      |
| Depth of Cut @ 45°   | 40 mm       |
| Depth of Cut @ 50°   | 36 mm       |
| Bore Diameter        | 20 mm       |
| Noise sound pressure | 91 dB(A)    |
| Noise sound power    | 102 dB(A)   |
| Noise K factor       | 3 dB(A)     |
| No Load Speed        | 3700 rpm    |



- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- Double safety trigger.
- High comfort grips.
- Removable dust nozzle.