

40VMax Orbital Sander XGT®, BO005CGZ

Square: 80 x 130 mm



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Orbits per Minute	6000 - 10000 min ⁻¹
AWS ready	✓
Sanding Pad Dimensions	80 x 130 mm
Sanding Orbit Diameter	3 mm
Product net weight	0,93 kg
Sound Pressure Level (L _{pA})	73 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,7 - 2,9 kg
Product Dimensions (L x W x H):	236 x 80 x 99 mm
Vibration Level, Sanding Metal Plate	2,6 m/s ²
Vibration Uncertainty (K Factor), Sanding Metal Plate	1,5 m/s ²

User benefits

- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Brushless maintenance-free and long-life motor

EAN 0197050005601

Link to product - www.makita.uk.com



Related products

Standard AC

122G32-0

Dust Bag Assy



413Y47-9

Front Cuff 22



413Y91-6

Pad Protector



Optional AC

1914H5-2

Battery Adapter Set 5m for XGT®



1914H7-8

Protection Cover Set



1914H8-6

Harness for 40V Max XGT® Sanders



1914H9-4

Square Pad Set 80x133mm



1914J0-6

Triangle Velcro Backing Pad



Other

User manual

Parts drawing