

Product datasheet

Specifications



Thorsman Glands - cable gland - grey - M12 - diameter 3 to 6.5

Local distributor code:

398239350

ISM71501

EAN Code: 3606480077180

Main

product range	Thorsman Glands
product type	Cable gland
colour	Grey (RAL 7035)
quantity per package	Set of 20

Complementary

Material	PA6
ISO thread	M12
Cable outer diameter	3...6.5 mm

Environment

IP-Class	IP68
operating temperature	-30...80 °C permanently -30...150 °C intermittently

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	14.500 cm
Package 1 Length	0.800 cm
Package 1 Weight	5.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	2.000 cm
Package 2 Width	14.500 cm
Package 2 Length	16.000 cm
Package 2 Weight	104.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	2500
Package 3 Height	27.000 cm
Package 3 Width	37.500 cm
Package 3 Length	55.000 cm

Package 3 Weight 13.400 kg

Logistical informations

Country of origin TR

Contractual warranty

Warranty (in months) 18



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	Nej