

Technical data sheet

Article number:
924-00388

SD1-4

Product Group	Spade/Forks Terminals
Product Family	Double Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Red (RD)
Application Range	Low Voltage
Conductor Size Range mm²	0.5-1.5 mm ²
Diameter (D)	4.3 mm
for Hole Ø (FH)	4.3 mm
Length (L)	21.5 mm
Length (L2)	10 mm
Length (L3)	11.5 mm
Max Current	19 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	7.2 mm

RoHS 