



Recipro Saw JR3051T

High power and more compact



Smooth cutting

in wood and metal cutting applications



Fixed shoe
For added durability

Longer 30 mm (1-3/16") stroke
for faster cutting performance

Large 2-finger trigger
for added convenience

Soft grip
handle provides increased comfort on the job.

Toolless blade change
for fast blade installation and removal

Accessory

Hook set
allows to hang the machine on ladder rungs or guard rails of aerial work platform. (country-specific)



Part No. 191C05-0



Recipro Saw	JR3051T	303 mm
Double Insulation	Continuous Rating Input 1,200W	
Variable Speed	Length of Stroke 30 mm (1-3/16")	
Carrying Case	Strokes Per Minute (SPM) 0 - 3,000	
Standard Equipment: Recipro Saw Blades	Capacity Pipe: 130 mm (5-1/8") Wood: 255 mm (10")	
	Vibration Level Cutting Boards: 19.5 m/s ² Cutting Wooden Beams: 19.5 m/s ²	
	Sound Pressure Level 88 dB(A)	
	Sound Power Level 99 dB(A)	
	Dimensions (L x W x H) 447x97x176 mm	
	Net weight 3.2 - 3.3 kg (7.1 - 7.3 lbs.)	
	Power Supply Cord 2.5 m (8.2 ft)	

The weight may differ depending on the attachment(s). The lightest and heaviest combination, according to EPTA-Procedure 01/2014, are shown in the table. Items of standard equipment and specifications may vary by country or area.

Makita Singapore Pte Ltd

7, Changi South Street 3, Singapore 486348
Phone : +65-6546-8700 Fax : +65-6546-8711
Email : msgproductteam@makita.com.sg
Website : www.makita.com.sg
Facebook : www.facebook.com/MakitaSG



VISIT OUR WEBSITE

PRINTED IN SINGAPORE