

## BENT TAP CONNECTOR



PART No.	SIZE MM X BSP	BAG QTY	BOX QTY
<b>PEMBTC1014</b>	<b>10 x 1/2"</b>	<b>10</b>	<b>150</b>
<b>PEMBTC1514</b>	<b>15 x 1/2"</b>	<b>5</b>	<b>50</b>

Suitable for central heating systems.  
With brass swivel nut and sealing washer.  
For torque figures see Technical Checklist.

## STOP END



PART No.	SIZE MM	BAG QTY	SMALL BOX	LARGE BOX
<b>PSE4610W</b>	<b>10</b>	<b>10</b>	<b>300</b>	
<b>PSE4615W</b>	<b>15</b>	<b>10</b>	<b>200</b>	<b>1000</b>
<b>PSE4622W</b>	<b>22</b>	<b>5</b>	<b>80</b>	<b>500</b>
<b>PSE4628W</b>	<b>28</b>	<b>5</b>	<b>50</b>	

Suitable for central heating systems.

## REDUCER



PART No.	SIZE MM	BAG QTY	SMALL BOX	LARGE BOX
<b>PEM061510W</b>	<b>15 x 10</b>	<b>10</b>	<b>150</b>	<b>1000</b>
<b>PEM062215W</b>	<b>22 x 15</b>	<b>10</b>	<b>70</b>	
<b>PEM062815W</b>	<b>28 x 15</b>	<b>5</b>	<b>40</b>	
<b>PEM062822W</b>	<b>28 x 22</b>	<b>5</b>	<b>30</b>	

Suitable for central heating systems.

## TANK CONNECTOR



Requires hand tightening only.  
Maximum wall thickness of tank = 4mm.

PART No.	SIZE MM	BAG QTY	BOX QTY
<b>CM0715S</b>	<b>15</b>	<b>10</b>	<b>60</b>
<b>CM0722S</b>	<b>22</b>	<b>5</b>	<b>20</b>
<b>CM0728S</b>	<b>28</b>	<b>1</b>	<b>10</b>

Suitable for cold water tanks only.

## PLUG



PART No.	SIZE MM	BAG QTY	BOX QTY
<b>PL10</b>	<b>10</b>	<b>10</b>	<b>500</b>
<b>PL15</b>	<b>15</b>	<b>10</b>	<b>250</b>
<b>PL22</b>	<b>22</b>	<b>10</b>	<b>100</b>
<b>PL28</b>	<b>28</b>	<b>10</b>	<b>50</b>

Suitable for central heating systems.

## PIPE REPAIR KIT



PART No.	SIZE MM	BAG QTY	BOX QTY
<b>15RKP</b>	<b>15</b>	<b>1</b>	<b>80</b>
<b>22RKP</b>	<b>22</b>	<b>1</b>	<b>50</b>

Suitable for central heating systems.

Provides a simple way of repair on a rigid pipe run.  
Remove a damaged section of pipe and replace with a repair kit

## SLIP TEE CONNECTOR



PART No.	SIZE MM	BAG QTY	BOX QTY
<b>15TKP</b>	<b>15</b>	<b>1</b>	<b>80</b>
<b>22TKP</b>	<b>22</b>	<b>1</b>	<b>40</b>

Suitable for central heating systems.

Provides a simple way to break into an existing pipe run

## PLASTIC BACK PLATE ELBOW



PART No.	SIZE MM X BSP	BAG QTY	BOX QTY
<b>15PWB</b>	<b>15 x 1/2"</b>	<b>1</b>	<b>25</b>

Hot and cold water only, 65°C maximum.  
Protect from sunlight and frost.

## WING BACK ELBOW



PART No.	SIZE MM X BSPT	BAG QTY	BOX QTY
<b>UGPWB1514</b>	<b>15 x 1/2"</b>	<b>1</b>	<b>150</b>

Cold water only

## BULKHEAD ELBOW



PART No.	SIZE MM X BSPT	BAG QTY	BOX QTY
<b>CM551516W</b>	<b>15mm x 3/4"</b>	<b>5</b>	<b>25</b>

Not suitable for central heating systems.  
Hot and cold water only, 65°C maximum.

## 2 WAY DIVIDER



PART No.	SIZE MM	BAG QTY	BOX QTY
<b>CM2315W</b>	<b>15</b>	<b>5</b>	<b>50</b>

Not suitable for central heating systems.

## 4 WAY MANIFOLD



PART No.	SIZE MM	BAG QTY	BOX QTY
<b>SFM512210E</b>	<b>22 x 10</b>	<b>5</b>	<b>30</b>

Suitable for central heating systems.

## 4 PORT RAIL MANIFOLD



PART No.	SIZE MM	BOX QTY
<b>SFM522210E</b>	<b>22 x 10</b>	<b>10</b>
<b>SFM522215E</b>	<b>22 x 15</b>	<b>10</b>

Suitable for central heating systems.



FOR PIPE SEE PAGE 15