

Datasheet

SVGA Extension Cable



Specification

Article Number	Decription	Length
121-6627	SVGA HD15 Male to Female Extension Cable	0.5M
121-6629		1M
121-6631		2M
121-6632		3M
121-6634		5M
121-6635		10M
121-6636		15M
121-6637		20M
121-6638		25M

- Available in 0.5M, 1M, 2M, 3M, 5M, 10M, 15M, 20M & 25M Lengths
- SVGA Monitor Extension Cable - HD15 Male to Female

Super VGA cables constructed using UL2919 approved 28awg triple mini coaxial and 5 30awg conductor cables, this allows them to be used for extended distances. Triple shielded with copper braid, foil and drain wire.