



182.72.104.66HK..-2RSNadelhülsen

## Drawn cup needle roller bearings with open ends HK2220-2RS (Series HK..-2RS)

lip seals on both sides, to DIN 618

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	22 mm
D	28 mm
C1	20 mm Tolerance: 0/-0,3
rmin	0,8 mm
m	26 g Mass
Cr	13400 N Basic dynamic load rating, radial
Cor	22100 N Basic static load rating, radial
Cur	2800 N Fatigue limit load, radial
nG	7000 1/min Limiting speed for grease lubrication
Fett	
	IR17X22X23-XL Suitable inner ring

