



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 171367-1
MIC CAP 21P ASSY H

Customers Also Bought




TE Part #200277-2
FEMALE BLOCK 50 PL.




TE Part #2-179276-3
DYNAMIC 3200 HDR ASSY 2P H



TE Part #1445828-1
REC,11-6,FRE HNG,SM INS,STD KE



TE Part #3-917360-0
1.25 AF REC ASSY 30P B/TRAY




TE Part #1-174923-1
070 MLC W-W PLUG HSG 6P F/A



TE Part #171892-1
9CIR MIC PLUG HSG




TE Part #171829-1
MIC CAP 21P



TE Part #1-174928-1
070 MLC W-W CAP HSG 3P F/A



TE Part #175029-2
070 MLC TAB CONT LP



TE Part #1108780-1
MDL2-GR.O-8.B1-4

Documents

Product Drawings

MIC PLUG 21P W/CIRCUIT NUMBER

English

CAD Files

Customer View Model

ENG_CVM_CVM_171838-1_C.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_171838-1_C.3d_igs.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_171838-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[Crimping Receptacle Contacts of Multi-Interlock Connector \(MIC\)](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

Japanese

[AMP EXTRACTION TOOL FOR MULTI-INTERLOCK CONNECTOR P/N 723735-1](#)

Japanese