

Cable Shears



burnished, plastic coated



[95 11 165](#)



burnished, with two-colour dual component handles



[95 12 165](#)



chrome plated, insulated with two-colour dual component handles, VDE-tested

IEC 60900 DIN EN 60900 ASTM F1505



[95 16 165](#)



burnished, plastic coated

Style 2: protective captive spring in the joint



[95 21 165](#)



burnished, with two-colour dual component handles

Style 2: protective captive spring in the joint



[95 22 165](#)



chrome plated, insulated with two-colour dual component handles, VDE-tested

Style 2: protective captive spring in the joint

IEC 60900 DIN EN 60900 ASTM F1505



[95 26 165](#)

Description**Applications**

■ for cutting copper and aluminium cables, single and multiple wire








- not suitable for steel wire and hard drawn copper conductors
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- easy cutting with one-hand operation
- with guard
- adjustable screw joint, self-locking
- forged
- special tool steel, oil-hardened and tempered

Model 95 11 165 :

- universal use for dismantling and stripping

Model 95 12 165 :

- universal use for dismantling and stripping

No.	EAN 4003773-	 Ø mm	 mm ²	AWG	 mm	 g
95 11 165	040323	15.00	50.00	1/0	165	215
95 12 165	029182	15.00	50.00	1/0	165	250
95 16 165	039648	15.00	50.00	1/0	165	262
95 21 165 	069805	15.00	50.00	1/0	165	215
95 22 165 	069812	15.00	50.00	1/0	165	254
95 26 165 	069980	15.00	50.00	1/0	165	275

 New

technical change and errors excepted