

Features

- Switched
- Switched
- Double Pole
- 13A Fused
- Twin Earth
- With Flex Outlet
- 20mm Knockouts
- Supplied with 40mm deep mounting box
- Surface Mounting

RS PRO Fused Spurs

RS Stock No.: 0845495



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Suitable for domestic, commercial and industrial installations.
- Suitable for use with standard UK 13A plug tops
- Optional flex outlet is available through the front of the plate
- Flex outlet has cable restraint fitted

General Specifications

Dimensions (mm)	80 (W) x 80 (H) x 42 (D)
Plate Fixing Centres (mm)	60.3
Style	Metal Clad
Insert Colour	White
Product Marking	Fused
Warranty (Years)	20

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	2
Terminal Capacity - Solid (mm ²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
Flex Outlet Available	Yes
Flex Outlet Location	Front of Plate
Flex Outlet Dimension (mm)	Ø10
Switched	Yes
Double Pole Switch	Yes
Supplied Back Box Depth (mm)	40
Back Box Knockouts - Total (mm)	5 x Ø20
Back Box Earth Terminal Supplied	Yes
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	13

Approvals

Standards Met	BS 1363-4, BS 1362
---------------	--------------------