

Product data sheet

Specifications



Repacked 2 Socket-outlet, New Unica, complete product, 2P + E, 16A, French, with shutter, IP4X, painted, anthracite

NU406954W



This repacked option saves 0.986 over the standard condition

Main

Range	New Unica
Product or component type	Socket-outlet
Aesthetic name	Unica Pro
Device presentation	Complete product
Device mounting	Flush
Socket number	2
Outlet poles configuration	2P + E
Outlet standard deviation	French
Outlet standard description	Pin earth
Rated current	16 A

Complementary

Device application	Power supply
Cover type	With shutter
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
fixing mode	Screws
Colour tint	Anthracite (RAL 7021)
Connections - terminals	Screw terminals
Cable cross section	0...2.5 mm² cable(s), 2 - cable stiffness: flexible 0...2.5 mm² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	PC: mechanism cover
Surface finish	Painted
Quantity per set	Set of 1 flow-pack
Standards	IEC 60884-1 NF C 61-314

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product certifications	NF
Embedding depth	24 mm
Depth	47 mm
Width	85 mm
Height	125 mm
Product weight	0.099 kg
surface treatment	Painted
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP4X
Environmental characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	9.500 cm
Package 1 Length	13.000 cm
Package 1 Weight	110.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.288 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

1 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

52b60409-d705-46c7-9ba3-cc3ef6e307da

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins