

Features

- EMI/RFI Shielded
- Straight version
- Die casted zinc
- 25 Way
- Supports cable 3-13 mm

RS PRO D Sub Backshell

RS Stock No.: 0730241



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *EMI/RFI Shielded D-Sub backshell kit*
- *Backshell for D-sub connector 25 pin male/female*
- *Die casted Zinc, Nickel plated*
- *Long finger screws and strain relief set*

General Specifications

| | |
|--|---|
| Type | Backshell kit size 25/B |
| For use with | D-Sub Connector 25 pin |
| Material | Zinc, Ni-plated |
| Cable diameter | Supports cable diameter 3-13 mm |
| Cable outlet orientation | Straight |
| Cable strain relief | PC UL94 V0, inserts in 4 sizes: 4 - 9 mm |
| Jackscrews | Steel Ni plated, long version with black plastic knob |
| Jackscrew tread | #4-40 UNC |
| Jackscrew mounting torque | 50 Ncm |
| Assembly screws | Steel Ni plated, self-tapping M3X10 PH |
| Assembly screws mounting torque | 100 - 120 Ncm |
| Attenuation factor | > 40 dB between 30 MHz and 1 GHz |

Operation Environment Specifications

| | |
|-----------------------|------------------|
| Operating temperature | -40° C to 120° C |
|-----------------------|------------------|

Approvals

| | |
|------------|----------------|
| Compliance | RoHS and REACH |
|------------|----------------|

