

Axial cylindrical roller and cage assembly

K89308-TV (Series K893)

single direction, double row, suitable for combination with axial bearing washers

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Dc1	40 mm	
Dc	78 mm	
Dw	7 mm	
Ea	77 mm	
Eb	44 mm	
m	0,098 kg	Mass
Ca	123000 N	Basic dynamic load rating, axial
C0a	385000 N	Basic static load rating, axial
Cua	39500 N	Fatigue limit load
nG	4850 1/min	Limiting speed

n _{gr}	1770 1/min	Reference speed
	GS89308	Allocated housing locating washer
	WS89308	Allocated shaft locating washer



