

SHRINK-KON®



Schrumpfschlauch PLG in HSB-Box Heatshrink tubing PLG in HSB box

Produktbeschreibung/-vorteile:

- Strahlenvernetztes Polyolefin, dünnwandig
- Temperaturbereich -55° bis $+125^{\circ}\text{C}$
- Schrumpfvermögen 2:1
- Schrumpftemperatur ab 125°C
- Von 0,6 mm bis 25,4 mm Innendurchmesser
- Anreihbar
- Schnittlängenhilfsmaß
- Einfache Handhabung durch übersichtliche Kennzeichnung
- Sichtfenster zur Inhaltskontrolle und Eurolasche zum Aufhängen
- Unproblematische Entsorgung, da sortenrein

Typische Anwendungsgebiete:

Werkstatt, Installation, Labor, Kleinserienherstellung u.ä.m.

Product description/Advantages:

- *Cross-linked polyolefin, thin walled*
- *Temperature range from -55° to $+125^{\circ}\text{C}$*
- *Shrink ratio 2:1*
- *Shrinks at temperatures starting from 125°C*
- *Interior diameters from 0.6 mm to 25.4 mm*
- *Can be attached to each other*
- *Cut length auxiliary measure*
- *Clear marking makes it simple to handle*
- *Window to check contents and normed bracket for easy attachment*
- *Simple disposal*

Typical applications:

Workshop, installation, laboratory, job lot manufacture and much more.

Produkt-Nr. <i>Product No.</i>	Nenn Durchmesser vor Schrumpfung <i>Nominal size before shrinkage</i>		Durchmesser nach Schrumpfung <i>Expanded I.D.</i>	Wandstärke nach max. Schrumpfung <i>Wall thickness after max. shrinkage</i>	Inhalt pro Box/m <i>Contents per box/m</i>
	[mm]	[inch]			
HSB 46-▲	1,2	3/64	0,6	0,4	12,00
HSB 63-▲	1,6	1/16	0,8	0,4	12,00
HSB 93-▲	2,4	3/32	1,2	0,5	11,50
HSB 125-▲	3,2	1/8	1,6	0,5	11,50
HSB 187-▲	4,7	3/16	2,4	0,5	9,50
HSB 250-▲	6,4	1/4	3,2	0,6	7,50
HSB 375-▲	9,5	3/8	4,7	0,6	6,50
HSB 500-▲	12,7	1/2	6,4	0,6	6,00
HSB 750-▲	19,1	3/4	9,5	0,8	5,00
HSB 1000-▲	25,4	1	12,7	0,9	3,30

▲ = Standardfarben/Standard colours

0 = schwarz/black	2 = rot/red	4 = gelb/yellow	6 = blau/blue	9 = weiß/white	c = transparent
●	●	○	●	○	○