



USBポートから最大3台のモニターへ4K/60Hzの映像出力できる、USB A-HDMI×3ポートのディスプレイアダプタ。USB Type-C変換アダプタ付き。

USB-CVU3HD8 **NEW**

USB-HDMIディスプレイアダプタ（4K×3画面出力）

JANコード 4969887784228



仕様

USBハブ

インターフェース規格	USB仕様 Ver3.2 Gen1 (USB3.1/3.0) 準拠 (USB Ver2.0/1.1上位互換)
コネクタ形状 (PC接続側)	USB Type-A、USB Type-C ※USB Type-C変換アダプタ付き
コネクタ形状 (アップストリーム)	USB3.2 Gen1 (3.1/3.0) Aコネクタ オス
電源	バスパワー
変換先コネクタ	HDMI

映像出力ポート

ポート形状	HDMIタイプA(19pin) メス×3
対応解像度	最大3840×2160 (4K/60Hz) ×3
最大対応解像度	4K/60Hz
デュアルディスプレイ出力	対応 ※最大3画面まで
最大接続可能台数	3台 ※2セット使用することで最大6画面まで映像出力できます。(Macは最大4画面まで)

共通仕様

消費電流	最大900mA
動作温度・湿度	温度/0°C～40°C 湿度/5～80% 結露なきこと

保管温度・湿度	温度/-10°C～60°C 湿度/5～80% 結露なきこと
セット内容	本体、USB変換アダプタ（USB A-USB Type-C）、取扱説明書
ケーブル長	0.5m
サイズ	W116×D14×H61mm
重量	約114g

特長

USBポートから4K解像度かつ60Hzの滑らかな映像を、最大3画面同時に出力できるUSB-HDMI映像変換アダプタです。

最大4K解像度（3840×2160/60Hz）出力に対応しており、4K対応の大画面テレビやモニター、プロジェクターなどへ高精細な4K解像度を最大3画面同時に出力することができます。

USB A-USB Type-C変換アダプタを付属しているため、どちらのタイプのポートでもご使用頂けます。

本製品を2個使用することで1台のパソコンに対して最大6画面まで映像出力が可能です。（Macは最大4画面まで）
ノートパソコンの画面を含め最大7画面をマルチディスプレイ化することができます。

※フルHD解像度以下の場合に限ります。

ドライバをインストールするだけで、簡単に使用できます。

USBケーブルを別途用意する必要がないケーブル一体型です。

《ご注意》

本製品はパソコン本体のUSBポートに直接接続して下さい。USBハブや増設のUSBポートではご利用いただけません。

本製品では著作権保護された映像（ブルーレイ映画など）を再生出力することはできません。

DirectX、OpenGL等のAPIは対応していません。

4K解像度での出力はディスプレイが4K解像度に対応しており出力するコンテンツも4K解像度に対応している必要があります。

クローンモード（ミラーモード）での動画再生は対応していません。

本製品の取り外し・接続に関して基本的にプラグアンドプレイには対応しておりますが、まれにUSB認識のタイミングエラーにより正常に表示しない/動作しない場合があります。再度抜き差ししお試してください。これは本製品の不具合・故障ではありません。

本製品はWindows OS/mac OSが動作している状態で使用するものです。システム起動時やBIOS画面では動作しません。（表示しません。）

本製品はUSBポートから映像信号を変換し出力するものでありパソコンの性能に大きく左右されます。

必ず対応機種以上のパソコン環境にてご利用ください。

高速で画面を切り替えるゲームや動画再生については画面のコマ落ちなどが発生する恐れがあり推奨できません。

対応機種、対応接続機器・環境の場合であっても正常に動作しない場合がございます。

対応情報

対応OS	Windows 11・10 ※Windows11/10の場合、Windows Updateによりドライバがすでにインストールされている可能性があります。本製品を接続するだけで動作する場合はそのままご利用ください。本製品を接続しても映像が出力されない場合はドライバのインストールを行ってください。 macOS (Tahoe) 26、macOS (Sequoia) 15、macOS (Sonoma) 14、macOS (Ventura) 13
対応機種	Windows搭載（DOS/V）パソコン、Apple Macシリーズ 【Windows搭載(DOS/V)パソコン】 CPU/Intel Core i5-8500/2GHz以上、AMD Ryzen3 2300U/2GHz以上 RAM/8GBまたはそれ以上 HDD/30MB以上の空きディスク容量があること。 【Apple Macシリーズ】 対応OSが搭載されたMac機であること。 ※USBポートを持ち、パソコン本体メーカーがUSBポートの動作を保証している機種。 ※パソコン・USB機器により対応できないものもあります。

This USB-A to HDMI x 3 display adapter supports 4K/60Hz video output from a USB port to up to three monitors. It also includes a USB Type-C adapter.
USB-CVU3HD8

specification

USB hub

- Interface Standard : USB specification Ver. 3.2 Gen. 1 (USB 3.1/3.0) compliant (USB Ver. 2.0/1.1 upward compatible)
- Connector shape (PC connection side) : USB Type-A, USB Type-C
*USB Type-C conversion adapter included
- Connector shape (upstream) : USB3.2 Gen1 (3.1/3.0) A-type male connector
- power supply : Bus powered
- Destination Connector : HDMI

Video Output Port

- Port Shape : HDMI Type A (19-pin) female x 3
- Supported resolutions : Maximum 3840 x 2160 (4K/60Hz) x 3
- Maximum supported resolution : 4K/60Hz
- Dual Display Output : Supported
*Up to 3 screens
- Maximum number of connectable devices : By using two sets of three units, you can output video to up to six screens (up to four screens for Mac).

Common Specifications

- Current consumption : Max 900mA
- Operating temperature/humidity : Temperature: 0°C to 40°C
Humidity: 5 to 80% (no condensation)
- Storage temperature/humidity : Temperature: -10°C to 60°C
Humidity: 5 to 80% (no condensation)
- Set contents : Main unit, USB conversion adapter (USB A to USB Type-C), instruction manual
- Cable length : 0.5m
- Size : W116 × D14 × H61mm
- Weight : Approximately 114g

Features

- This USB-HDMI video conversion adapter can output smooth 4K resolution and 60Hz video from a USB port to up to three screens simultaneously.
- It supports output of up to 4K resolution (3840 x 2160/60Hz), and can output high-definition 4K resolution to up to three 4K-compatible large-screen TVs, monitors, projectors, etc. simultaneously.
- A USB A to USB Type-C adapter is included, so you can use either type of port.
- By using two of these products, you can output video to up to six screens on one computer (up to four screens on a Mac), allowing you to create a multi-display environment with up to seven screens, including your laptop screen.
*This applies only to full HD resolution or lower.
- Just install the driver and it's easy to use.
- It is an integrated cable type that does not require a separate USB cable.

Note:

This product must be connected directly to the computer's USB port. It cannot be used with a USB hub or an additional USB port.

This product cannot play or output copyright-protected video (such as Blu-ray movies). It does not support APIs such as DirectX or OpenGL.

4K resolution output requires a 4K-compatible display and the output content must also support 4K resolution.

Video playback in clone mode (mirror mode) is not supported.

While this product is generally plug-and-play compatible, there may be rare cases where the display or function does not work properly due to a timing error in USB recognition. Please try reconnecting and reconnecting. This is not a malfunction or defect of the product.

This product is intended for use with Windows OS/macOS. It does not work during system startup or at the BIOS screen (no display).

This product converts and outputs a video signal from the USB port, so its performance is highly dependent on the computer's performance.

Be sure to use it with a computer that meets or exceeds the supported specifications.

Games and video playback with fast screen changes are not recommended as they may cause frame drops.

Even with a compatible model, connected devices, and environment, proper operation may not be possible.