


TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



VARIAC

MODEL	CMV20E-1
INPUT	240V
OUTPUT 1	0-100%
OUTPUT 2	0-112%
RATED	20 AMPS

TERMINATIONS M5 STUDS

A	LIVE I/P FOR 100% O/P
B	LIVE I/P FOR 112% O/P
C	NEUTRAL I/P AND O/P
D	CENTRE TAP (FOR BUCK-BOOST)
E	LIVE O/P (VARIABLE)

REV	4	
	3	
	2	
	1	

CARROLL & MEYNELL TRANSFORMERS LIMITED TEL: 01642 617406 FAX: 01642 614178 enquiries@carroll-meynell.com	TITLE	DRAWN	PROJECTION	DATE	SCALE
	SPH VARIAC CMV20E-1	SH		30/4/8	NTS
	ALL DIMENSIONS IN mm	DRAW No		REV	PAGE
		6082		0	1/1