

HLM-15R0




- Strip Ties (HLS) - Rolls performed in convenient 6", 12" and 18" strips
- 15' & 75' Rolls (HLM/HLS-15 & 75) - Can be cut to desired length, eliminating waste
- Adjustable, releasable, and reusable hundreds of times – ideal for applications requiring frequent moves, adds, or changes
- Hook and loop material maintains network data integrity by protecting against over-tensioning of high performance copper and fiber cables
- Easy to use and operator safe with no sharp edges
- Complementary mounts available

Note: Minimum 2" overlap required to achieve loop tensile rating

Part Number	HLM-15R0
RoHS Compliancy Status	Compliant
Part Description	Hook & Loop Cable Tie, 15' roll, Miniature cross section
Product Type	Cable Ties
Material	Nylon Loop, Polyethylene Hook
Color	Black
CSA Certified	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	No
Length (ft.)	15.0
Length (In.)	180.0
Length (m)	4.6
Length (mm)	4572
Width (In.)	.330
Width (mm)	8.4
CE Compliant	Yes
Cross Section	Miniature
Locking Style	Hook & Loop
Max. Bundle Diameter (In.)	Various
Max. Bundle Diameter (mm)	Various
Min. Bundle Diameter (In.)	.25
Min. Bundle Diameter (mm)	6
Min. Loop Tensile Strength (Lbs.)	18
Min. Loop Tensile Strength (N)	80
Pricing Description	Hook & Loop Roll, 15' L(4.6m), .75"W (19.1mm), Black
Temperature Range	0°F to 220°F

▪ Thickness (In.)	.10
▪ Thickness (mm)	2.5
▪ Min. Order UOM	RL
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	MIN. LOOP** TENSILE lbs. (N)	APPROXIMATE WEIGHT lbs/10 ROLLS (g)
	MIN. in (mm)	MAX. in (mm)					
*HLM-15R	.25 (6.4)	VARIOUS	.100 (2.5)	180 (4572)	.330 (8.4)	18 (80)	.55 (251)




ILLUSTRATION 'A'

NOTES:

- * 1) PACKAGED IN 15 FT. ROLLS. (SEE ILLUSTRATION 'A')
- ** 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
- 3) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR OPTIONAL COLORS.

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS												
										SS_27052_02.PRT		
										<h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS		
										TAK-TY CABLE TIE CONTINUOUS 15FT. ROLL HLM SERIES		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .035 (.89mm) (.XX) ± ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY KET	MAT'L: POLYETHYLENE HOOK/ NYLON KNIT LOOP	SCALE NONE
3	04/12/06	FAB		ADDED WEIGHTS TO DRAWING	27052	3				DATE 08-20-96	DRAWING NO. SS-27052	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D HVP		