

Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

Adhesive	Permanent Acrylic
Article No.	131573
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	Black on Yellow/Transparent
Finish	Matt
Order Reference	M-91-427-YL
Printable Area - Height (mm)	12.70
Printable Area - Width (mm)	25.40
Printer Compatibility	BMP41; BMP51; BMP53
Size - Height (mm)	38.10
Size - Width (mm)	25.40
Additional Information	Self-laminating; Self-extinguishing; Excellent water & oil resistance; Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	180 Label(s) / Box
Vertical Repeat (mm)	41.28
Wire Gauge	10-4
Approval/Compliance	UL Recognised
Adhesive (Y/N)	Yes
Application	Voice & Data Communication; Wire & Cable Marking
Industry	Data & Telecommunications; Electrical
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	8.10
Min. Service Temp. °C	-80

Min. Wire/Cable Diameter (mm)	4.00
Shape	Rectangle
Software	LabelMark
Surface	For smooth & textured/rough surfaces
Voice/Data Application	CAT 6; 4 pair UTP Copper