







MARKING:



MARKING:




WIRING COLOR:

E: Yellow/Green
N: Blue
L: Brown

LENGTH ON CORD: (205-14)

I-SHENG SGIS <VDE> KEMA-KEUR <VE> <VE> △CEBEC 809 ⓈⓄⓈⓈ
NF-USE 1346 IEMMEQU H05VV-F 3G 1.0mm² 60227 IEC 53 RVV 300/500V Ⓢ
A003083 3ASL/100 4V-75 V-75(75°C) 250/440V ORDINARY DUTY Q90033 -LF- CE

No	BOM ITEM	Q'TY	P/N
1	SP-023 INSERT(BLACK)	1 pcs	MB023012
2	PVC 45P (SA87, SP-022)	33 g	RPP04512
3	KPR-14 TERMINAL	3 pcs	BBB14000
4	IS-14 INNER BODY	1 set	MI014000
5	PVC 45P (SA87, IS-14)	22 g	RPP04512
6	PE TIE (BLACK, 6 inch)	1 pcs	KBB10006

CABLE	H05VV-F 3G 1.0 DENT PRINT CT-12 (BLACK)			
PLUG	SP-022 + IS-14	LENGTH	1000	UNIT mm
CLIENT	NAME	First Connectiviey	N/W	0.139821 UNIT kg
	P/N	6266751	SG DWG	SR-141586-2 VER. A
	I-SHENG MANUFACTURING (SONG GANG) FACTORY 松崗鎰勝製品廠		Design. by	楊望春 6/27-10
			Review. by	張曉玲 6/27-10
			Approval. by	6/26/2010
V24 6C3016 12 100 00				