

#### **FEATURES**

- Red 0.5-1.5mm<sup>2</sup>
- Blue 1.5-2.5mm<sup>2</sup>
- Yellow 4-6mm²

# RS PRO Insulated Ring Terminal, M8 Stud Size, 2.5mm<sup>2</sup> to 6mm<sup>2</sup> Wire Size, Yellow

RS Stock No.: 534-424



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## **Ring Terminals**



### **Product Description**

A PVC Funnel Entry range of crimps on Reels. Available in a variety of the most popular sizes.

#### **General Specifications**

Insulation	Insulated
Insulation Material	PVC
Colour	Yellow
Contact Material	Copper
Contact Plating	Tin
Stud Size	M8

#### **Mechanical Specifications**

Thickness	1mm
Overall Length	34.2mm
Inner Ring Diameter	8.4mm
Outer Ring Diameter	14mm
Maximum Wire Size	6mm^2
Minimum Wire Size	2.5mm^2
Maximum Wire Size (AWG)	10AWG
Minimum Wire Size (AWG)	12AWG




### **Approvals**

Compliance/Certifications

2011/65/EU and 2015/863





## Ring Terminals



Insulated	Wire	range	Dimensions					Stud size	
Stock no.	AWG	mm²	Colour	В	D	L	1	AWG	mm
534238	22-16	0.5-1.5	Red	5.5	4.3	16.0	9.9	4	3.2
534222	22-16	0.5-1.5	Red	6.6	4.3	18.7	9.9	6	3.7
534216	22-16	0.5-1.5	Red	8.0	4.3	21.0	9.9	8	4.3
534200	22-16	0.5-1.5	Red	8.0	4.3	20.5	9.9	10	5.3
534193	22-16	0.5-1.5	Red	11.0	4.3	25.5	9.9	1/4	6.4
2082492	22-16	0.5-1.5	Red	12.0	4.3	27.0	9.5	5/16	8.4

Stock no.	AWG	mm²	Colour	В	D	L	1	AWG	mm
534597	16-14	1.5-2.5	Blue	6.7	4.8	19.0	9.9	6	3.7
534581	16-14	1.5-2.5	Blue	8.0	4.8	20.5	9.9	8	4.3
534575	16-14	1.5-2.5	Blue	9.5	4.8	22.0	9.9	10	5.3
534569	16-14	1.5-2.5	Blue	10.5	4.8	26.0	9.9	1/4	6.4
2082509	16-14	1.5-2.5	Blue	12.0	4.8	27.5	9.9	5/16	8.4

Stock no.	AWG	mm²	Colour	В	D	L	ı	AWG	mm
534468	12-10	2.5-6.0	Yellow	7.2	6.5	27.0	13.5	6	3.7
534452	12-10	2.5-6.0	Yellow	9.5	6.5	26.5	13.5	8	4.3
534446	12-10	2.5-6.0	Yellow	9.5	6.5	27.0	13.5	10	5.3
534430	12-10	2.5-6.0	Yellow	11.0	6.5	29.0	13.5	1/4	6.4
534424	12-10	2.5-6.0	Yellow	14.0	6.5	34.0	13.5	5/16	8.4
2082537	12-10	2.5-6.0	Yellow	15.0	6.5	35.5	13.5	3/8	10.0