

## **Datasheet**

**ENGLISH** 

## RS Pro 2, 3, 4 & 5 WAY M12 PUSH-PULL SQUARE FLANGE MALE



## Specifications:

From RS Pro, these push-pull plugs are serious contenders for your application. The convenient push-pull connection, makes it perfect in situations where accidental disconnects occur. That coupled with the IP67 rating, makes sure that this industrial connector excels in harsh environments. When choosing a male connector, this version should really be one you consider.



## ENGLISH

Coupling Type	Push and Pull
P Rating	IP67
Material	Metal
Shell	Brass with chrome plating
Insert material	PPS max temperature 260°C , fire resistance:V-0
Contact material	Brass with gold plating
Termination	Solder
Cable outer diameter range	I : 4-6.5mm II : 5-8mm
Mating cycle	> 500
Temperature range	-40~+85°C
Insulation resistance MΩ	2000