



1610EU Protector

The Peli 1610 is a large sized protector case that comes with 2 comfortable, fold down carrying handles as well as a retractable handle and 2 strong polyurethane wheels with stainless steel bearings. Like all other Peli Protector cases, this rugged case is also designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid and stainless steel hardware. Rugged, uncompromising and trusted, Peli cases protect what matters to you, from the everyday to the extraordinary. Peli Protector Cases are made with copolymer polypropylene and cutting edge technology, which makes them virtually indestructible and resistant to the most extreme conditions. Proven for over 45 years in the most demanding environments. Engineered and manufactured in the U.S and in Germany. Guaranteed for Life and sustainable due to its long life.

- **Strong polyurethane wheels with stainless steel bearings**
- **Watertight, crushproof, and dustproof**
- 3 level Pick N Pluck™ with convoluted lid foam
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Easy open double-throw latches
- Fold down handles
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Retractable extension trolley handle
- Stainless steel hardware and padlock protectors
- Made in Germany



CONFIGURATIONS



1610EU
Standard



1614
With Padded Dividers



1610NF
No Foam



1610WF
With Foam

DIMENSIONS

Interior (L×W×D)	21.68 x 16.62" x 10.56 (55.1 x 42.2 x 26.8 cm)
Exterior (L×W×D)	24.71 x 19.58" x 11.93 (62.8 x 49.7 x 30.3 cm)
Lid Depth	2.06" (5.2 cm)
Bottom Depth	8.50" (21.6 cm)
Total Depth	10.56" (26.8 cm)
Int Volume	2.2 ft³ (0.062 m³)
Padlock Hole Diameter	5/16" (12.7 cm)

MATERIALS

Body	Polypropylene
-------------	---------------

Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS

 Black

WEIGHT

Weight With Foam	22.49 lbs (10.2 kg)
Weight Empty	20.00 lbs (9.07 kg)
Buoyancy	119.93 lbs (54.4 kg)
Master Pack Weight	25.55 lbs (11.59 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	190°F (87.8 °C)

CERTIFICATIONS

IP67
Def Stan 81-41

OTHER

Wheels	2
Extendable Handle	yes
Master Pack	1
Nameplate	yes
Military	yes

ACCESSORIES



1609
Lid Organizer



1611
5 pc. Replacement Foam Set



1615
Padded Divider Set



1623
Replacement O-ring



1610EUTP
TrekPak Case Divider Kit



1507QM
Quick Mounts - set of 4



1506TSA
TSA Lock



1500D
Desiccant Silica Gel

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 08-19-26