



LENOX Bi-metal Jig Saw Blade – Med Metal

20308BT518S



- Super sharp to cut fast without deflection
- Milled to precision sharpness for straight cuts and a smooth finish
- Designed for optimal performance in cutting medium metal
- Shatter resistant with bi-metal technology

Description:

The LENOX Bi-metal T-Shank Jig Saw Blade 135mm has been constructed using bi-metal technology which flexes and resists breaking, delivering extended blade life. The milled to precision sharpness of the blade for straight cuts provides a smooth finish. The super sharp blade enables for fast precision cutting without deflection. Ideal for cutting medium metal.

Specifications	
TPI	18
Size	135 x 10 x 1.3 mm
Blade Quantity	2