

Pole hedge trimmer LXT®

DUN461W

18V • 460 mm

Model DUN461W is a pole hedge trimmer equipped with a telescopic pole, powered by 18V Li-Ion battery.

This Pole Hedge Trimmer enables to trim tall hedges or prune twigs or thin branches from tall trees without using a stepladder.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	3600 min ⁻¹
Length Of Blade	460 mm
Max blade opening	18 mm
Angle range vertical	135 °
Continuous Use 18V / 5.0 Ah Battery	122 min
Continuous Use 18V / 3.0 Ah Battery	60 min
Sound Power Level (L _{WA})	85 dB(A)
Sound Pressure Level (L _{pA})	73 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Telescopic pipe for no need of stepladders
- Battery protection circuit protects against overloading, over-discharging and over-heating
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Related products

Optional AC

794530-8

Diamond file, Ø 4,0 mm

Other

User manual

Parts drawing