



Professional Microfibre Cloths







Low cost Microfibre that delivers superior cleaning performance and durability.

- 80% Split Microfibre
- 20% Polyester
- Very durable - Withstands up to 300 laundering cycles and drying cycle without bleach (Wash temperature: 95°C)
- Bleach resistant, withstands up to 100 laundering cycles (with bleach)
- Thicker 200 gr/m² cloth , better debris pick up and absorption
- Cleans better and lasts longer
- Colour-coded products help reduce cross contamination by differentiating area of use
- Consistent with HACCP thanks to colour coding
- Highly absorbent
- Proven to remove 99.9% of microbes



PRODUCT INFORMATION

Ref	Description	Material	Dimensions (cm)	Colour	Pack
1865827	Professional MF Cloth Red	Microfibre	40.6 x 40.6		12 cloths per polyabg; 10 polybags = 120 cloths
1865828	Professional MF Cloth Green	Microfibre	40.6 x 40.6		12 cloths per polyabg; 10 polybags = 120 cloths
1865829	Professional MF Cloth Blue	Microfibre	40.6 x 40.6		12 cloths per polyabg; 10 polybags = 120 cloths
1865830	Professional MF Cloth Yellow	Microfibre	40.6 x 40.6		12 cloths per polyabg; 10 polybags = 120 cloths

SHIPPING INFORMATION

Ref	CoO	EAN Product	DUN Carton	Custom Code	Carton Dimensions (cm)	Weight (kg)
1865827	China	5453001914213	05453001914213	6307103000	42 x 42 x 23	4.56 kg
1865828	China	5453001914220	05453001914220	6307103000	42 x 42 x 23	4.56 kg
1865829	China	5453001914237	05453001914237	6307103000	42 x 42 x 23	4.56 kg
1865830	China	5453001914244	05453001914244	6307103000	42 x 42 x 23	4.56 kg