

NPG-M321B



Products → Low Voltage Products and Systems → Installation Products
→ Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

General Information

Extended Product Type:	NPG-M321B
Product ID:	7TCA303070R0004
EAN:	5415022403282
Catalog Description:	QUICK CONN CG 32MM 15-21MM NYL BLK
Long Description:	Quick Connect Cable Gland, Thread Size M32, Cable Range 15 to 21 Millimeters, Thread Length 9 Millimeters, Nylon, Black

Ordering

EAN:	5415022403282
Minimum Order Quantity:	5 piece
Customs Tariff Number:	3917400090

Dimensions

Product Net Weight:	4.536 g
----------------------------	---------

Container Information

Package Level 1 Units:	5 piece
Package Level 1 Width:	89.916 mm
Package Level 1 Height:	89.916 mm
Package Level 1 Depth / Length:	180.086 mm
Package Level 2 Units:	20 piece
Package Level 2 Width:	400.05 mm
Package Level 2 Height:	279.908 mm
Package Level 2 Depth / Length:	100.076 mm

Additional Information

Brand / Label:	T&B
Color:	Black
Function:	General purpose, Ideal for Panel building and Volume Installers
Material:	Nylon
Product Main Type:	CABLE GLANDS AND ACCESSORIES
Product Name:	Nylon Cable Gland
Product Type:	Quick Connect Cable Gland
Standards:	cULus, RoHS, WEEE, LVD

UPC: 786210137858

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: TDS000036

Instructions and Manuals: NPG-M321B

Classifications

ETIM 6: EC000441 - Cable screw gland

UNSPSC: 39121431

