

Scarifier XGT®

UV001GZ

40V max, 380mm, 50 L

Model UV001G is a cordless Scarifier powered by 40Vmax XGT® Li-Ion battery (two in parallel or one).



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Working width	380 mm
No load speed	3200 min ⁻¹
Rear Wheel Diameter	18 cm
Front Wheel Diameter	18 cm
Working Depth	-12 - +5 mm
Collecting Box Capacity	50 L
Sound Power Level (L _{WA})	86 dB(A)
Sound Pressure Level (L _{pA})	74 dB(A)
Product net weight	16,5 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	18,7 - 23,8 kg
Product Dimensions (L x W x H):	1020 - 1240 x 680 x

User benefits

- Two different blades available for different applications, vertical cutter and thatching blade

EAN 0197050000545

Link to product - www.makita.uk.com



Related products

Standard AC

1913J7-6

Thatching Blade Set



782223-9

Socket wrench



Other

User manual

Parts drawing