

Cable housing - KGG-PC 4/ 4-F - 1837337

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Cable housing, Pitch: 0 mm, Number of positions: 4, Dimension a: 32.28 mm, Color: green



Why buy this product

- Ergonomic cable housing for standard PC 4 plugs with screw connection
- KGS-PC 4 (angled cable outlet) for cable diameters from 6 to 16 mm²
- A cable clamp can be mounted back to front
- KGG-PC 4 for cable diameters from 4 to 13.5 mm²



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 111342
Weight per Piece (excluding packing)	18.6 g
Custom tariff number	85369010
Country of origin	Poland

Technical data

Dimensions

Pitch	0 mm
Dimension a	32.28 mm

General

Range of articles	KGG-PC 4/...-F
Insulating material group	0
Insulating material	ABS
Inflammability class according to UL 94	HB
Number of positions	4

Cable housing - KGG-PC 4/ 4-F - 1837337

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC000058
ETIM 4.0	EC000437
ETIM 5.0	EC000451

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

GOST / GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--

Cable housing - KGG-PC 4/ 4-F - 1837337

Approvals



Accessories

Accessories

Terminal marking

Marker for terminal blocks - SBS 2,5/7,5 - 1007604



Marker for terminal blocks, Card, white, Unlabeled, Can be labeled with: Plotter, Perforated, Mounting type: Snap into tall marker groove, Snap into flat marker groove, Lettering field: 15 x 7.5 mm

Cable housing - KGS-MSTB 2,5/ DST - 1784914



Transparent label carrier, can be marked with marker strips SBS 2.5/7.5

Drawings

Dimensioned drawing

