

LED RECHARGEABLE LASER PENLIGHT

Product Specifications

SPECIFICATIONS	OBS-PL2
Color	Grey/Red
Material	Aluminum/Plastic
Luminosity (Lumen)	400 (Turbo Mode) 250 (Front Flood Light - High Mode) 30 (Front Flood Light - Low Mode)
Rechargeable	Yes
Battery Type	Lithium-Ion
Runtime	30s (Turbo Mode) 2h (Front Flood Light - High Mode) 24h (Front Flood Light - Low Mode)
Charge Time	2h
Charging Port	USB-C
Weight	2.2 oz / 62 g
Length	6.9 in / 175 mm
Width	0.7 in / 17 mm
Height	0.7 in / 17 mm
Storage/Operating Temperature	+15°F to +120°F / -10°C to +50°C
IP Rating	IP65
IK Rating	IK07
Laser	Yes (Class II)
Dimming	Yes
Rotating, Magnetic Clip	Yes
Accessories	Charging Cable