

Fan XGT®

CF001G

40V max • ø 235 mm • 8.2 m³ / min

Three blowing speeds and a timer function

This 235 mm XGT® battery or AC powered fan is an excellent companion for the summer heats. It is equipped with oscillation (45° L/R), adjustable fan head angle, 3 wind speed settings and an timer function. Fan blades are easy to clean-up. Quiet running, only 48 dB(A) in high speed mode.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Max. Air Velocity	2,0 / 2,5 / 3,16 m/s
Air volume	8,2 / 6,5 / 5,2 m³ / min
Continuous use XGT® 40Vmax / 2.5 Ah	730 / 550 / 410 min
Continuous Use XGT® 40V Max / 4.0 Ah	19 / 14,5 / 11 h
Diameter (D)	235 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	2,7 - 3,3 kg
Product net weight	2,0 kg
Product Dimensions (L x W x H):	143 x 333 x 463 mm
Angle range horizontal	180 °
Angle range vertical	135 °
Automatic rotational angle (left / right)	45 °

User benefits

- Three speed settings (High/Medium/Low)
- Powered by Makita XGT® Li-ion battery or AC adapter
- Automatically swings 45° L/R
- Fan head angle can be adjusted from side to side and up and down (Up 90°, Down 45°, Right and Left 90°)
- 3-stage automatic timer with 1, 2, and 4 hour power-off selection
- Carry handle for easy transportation
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing