



PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 9:21 (UTC)



7310BEAT85

Single-Row Angular Contact Ball Bearings

Parts Number

7310BEAT85SUCNB

Boundary Dimensions

d	50	mm	Bore diameter
D	110	mm	Outside diameter
B	27	mm	Width
r (min.)	2	mm	Chamfer dimension
r1 (min.)	1	mm	Chamfer dimension

Basic Load Ratings

Cr	82000	N	Basic dynamic load rating
C0r	50500	N	Basic static load rating

Speeds

Grease	5600	min-1	Grease lubrication
Oil (Oil-bath)	8000	min-1	Oil-bath lubrication

Dimensions

a	47.1	mm	Effective load center
---	------	----	-----------------------

Abutment and Fillet Dimensions

da (min.)	60	mm	Diameter of shaft abutment
Da (max.)	100	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Mass

Mass approx.	1.07	kg	Mass approx.
--------------	------	----	--------------

