LS1D32

Poles description

TeSys fuse-disconnector - 3 poles - 32A - fuse size 10 x 38 mm

Product availability: Stock - Normally stocked in distribution facility



Main Commercial Status Commercialised Range of product TeSys fuse-disconnector Product or component Fuse-disconnector type Device short name LS1 D 3P

Complementary

Mounting support	Rail	
Mounting position	Vertical +/- 23°	
Control type	Toggle	
[Ue] rated operational voltage	60 V for signalling circuit 250 V for signalling circuit 690 V for power circuit	
[le] rated operational current	25 A for power circuit 6 A for signalling circuit	
Fuse size	10 x 38 mm	
Fuse type	AM GG	
Connections - terminals	2 flexible cable(s) 00.01 in² (14 mm²) with cable end on screw clamp terminals for power circuit 2 flexible cable(s) 00.01 in² (1.56 mm²) without cable end on screw clamp terminals for power circuit 2 solid cable(s) 00.01 in² (16 mm²) on screw clamp terminals for power circuit	
Tightening torque	15.04 lbf.in (1.7 N.m) power circuit: on screw clamp terminals	

Environment

Standards	IEC 60947-3
Product certifications	BV UR
Protective treatment	TH
Ambient air temperature for operation	-58158 °F (-5070 °C)
Height	3.5 in (89 mm)
Width	1.77 in (45 mm)
Depth	2.69 in (68.3 mm)
Product weight	0.66 lb(US) (0.3 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS	
Discount Schedule	112	
GTIN	00785901046981	
Nbr. of units in pkg.	1	
Package weight(Lbs)	0.42	
Product availability	Stock - Normally stocked in distribution facility	

Returnability	Υ	
Country of origin	MX	

Contractual warranty

	· ·
Period	18 months

