



ENGLISH

Datasheet

RS Pro Recordable Sea Scope

RS Stock 913-1579



The RS Pro recordable sea scope waterproof video inspection system. This video inspection system comes with a monitor, camera-tipped probe and an IP67 rated waterproof grip.

This device makes it possible to inspect sewer, water lines and view video underwater in real time.

Features and Benefits

- Photo & Video Recordable
- Great design with ZOOM IN ZOOM OUT function
- 1/9" VGA CMOS
- Unique design with SCREEN UPSIDE DOWN function
- TV Video
- Micro SD video record function
- PE Covered Flexible Gooseneck; ABS Handler
- Rigid carry case
- Hook, Magnet & Mirror

Technical Specification

With monitor	YES
MONITOR removable	NONE
Wireless between monitor and handle	NO
Whole unit waterproof	YES IP67 (1 meter 30 minutes)
Handle water resistant	YES IP67 (1 meter 30 minutes)
Probe waterproof	YES IP67 (1 meter 30 minutes)
Monitor Resolution	320 x 234 Pixels
Monitor size	3.5"
Support Video Recording	YES
Support microSD card	Max. 32GB
Support ZOOM	4 times
CAMERA SENSOR Resolution	640 x 480 Pixels
White comparison	automatic
Exposure to light	automatic
Support Video Out	YES
Camera illumination	2 LEDs, white
USB port	USB1.1
Power Supply	4 x 1.5V AA Max. 450mA
Operating temperature	0 to+45°C
Operating Humidity	15 - 85% RH
Storage temperature	.-10 to +50°C
Storage Humidity	15 - 85% RH
Metal tube length	88.0 +- 2.0 cm
Total length of device	131.0 +-2.0 cm
Minimum Bending radius	4.5 cm
Diameter of camera head	8.0 mm
Lens coverage	54°
Focus	> 3 cm
Weight without accessories	Approx. 500 g
Flexible gooseneck outer	Diameter 6.8 mm.

Standards

IP67

Note

AA battery not included

Application Information

The RS Pro Recordable Sea Scope is also ideal for marine search and rescue operations.